



Evolution[®] 100



Category Benefits

- Food waste is ground into particles and flushed away in seconds
- Clean, hygienic, convenient and simple to use
- Easy method to manage food waste in the home, saving you time and helping to minimise trips to the outside rubbish bin
- Easy to install into new or existing kitchens and can be fitted to most sinks
- Environmentally responsible, helping reduce the amount of waste that goes to landfill sites

Features

- Evolution quiet technology
- Evolution 2-stage grind technology
- Auto-reverse grinding action
- High-torque Dura-Drive[™] induction motor
- Built-in air switch with chrome button
- Compact design
- 5 Year guarantee
- Stainless steel grind elements
- Overload protection
- Quick Lock[®] mounting assembly for faster, easier installation


Sample Specification

Food waste disposer(s) shall be InSinkErator[®] Model Evolution 100 with 2-stage grind and quiet technologies, .75 hp (220-240V) motor, auto-reverse grind system, stainless steel grind chamber, grinding elements and built-in air switch in chrome.

Guarantee: 5 Year parts and service.

The complete InSinkErator guarantee is included in the Care & Use Booklet packed with each unit.

Dimensions (cm)



| Evolution 100 | | | |
|---------------|------|---|------|
| A | 31.1 | D | 22.2 |
| B | 17.1 | E | 16.8 |
| C | 6.4 | | |

InSinkErator reserves the right to change product specifications without prior notice. The disposer described in this leaflet is for household use; usage in commercial situations is not covered by warranty.

Specifications

| | | | |
|---------------------------|-----------------------------------------------|-----------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Type of Feed | Continuous | Sound Technology | Anti-Vibration Mounting and Tailpipe Quiet Sink Baffle Multi-Layer Sound Insulation Premium Stainless Steel Stopper |
| On/Off Control | Wall Switch or Built-In Air Switch | Grind Chamber Capacity | 1005 ml |
| Motor | Single Phase | Motor Protection | Manual Reset Overload |
| Reversing | Auto-Reverse Grind System | Average Water Usage | Approximately 1% of household water consumption |
| Time Rating | Intermittent | Average Electrical Usage | 3-4 KWH p.a, equal to approx. \$3.50 p.a |
| Lubrication | Permanently Lubricated Upper & Lower Bearings | Drain Connection | 1-1/2" (3.81 cm) Anti-Vibration (Hose Clamp) |
| Shipping Weight (Approx.) | 10.0 kg | Dishwasher Drain Connection | No |
| Unit Finish | Gray | | |
| Overall Height | 31.1 cm | | |
| Grind Technology | 2-Stage Grind Technology | | |

| Volts/Hz | HP | Average Load |
|--------------------|------------------|--------------|
| 120V, 60 Hz | .75 | 9.5 A |
| 110-127V, 60 Hz | .75 | 9.5 A |
| 220-240V, 50-60 Hz | .75 (@240V/50Hz) | 380 W |

InSinkErator Australia
Sales/Service Tel: 1300 136 205

www.insinkerator.com.au



InSinkErator reserves the right to change product specifications without prior notice. All products are for household use; usage in commercial situations is not covered by warranty.