



Evolution[®] 200

Category Benefits

- Food waste is ground into particles and flushed away in seconds
- Clean, hygienic, convenient and simple to use
- Easy method to manage food waste in the home, saving you time and helping to minimise trips to the outside rubbish bin
- Easy to install into new or existing kitchens and can be fitted to most sinks
- Environmentally responsible, helping reduce the amount of waste that goes to landfill sites

Features

- Evolution ultra-quiet technology
- Evolution 3-stage grind technology
- Auto-reverse grinding action
- High-torque Dura-Drive™ induction motor
- Built-in air switch with chrome button
- 6 Year guarantee
- Stainless steel grind elements and grind chamber
- Overload protection
- Quick Lock[®] mounting assembly for faster, easier installation

Sample Specification


Food waste disposer(s) shall be InSinkErator[®] Model Evolution 200 with 3-stage grind and ultra-quiet technologies, 1 hp (110-120V) or .75 hp (220-240V) motor, auto-reverse grind system, stainless steel grind chamber, grinding elements and built-in air switch in chrome.

Guarantee: 6 Year parts and service.

The complete InSinkErator guarantee is included in the Care & Use Booklet packed with each unit

Specifications

Dimensions (cm)



Evolution 200			
A	33.0	D	23.4
B	18.5	E	16.8
C	6.4		

InSinkErator reserves the right to change product specifications without prior notice. The disposer described in this leaflet is for household use: usage in commercial situations is not covered by warranty.

Type of Feed	Continuous	Sound Technology	Anti-Vibration Mounting and Tailpipe Quiet Sink Baffle Multi-Layer Sound Insulation Premium Stainless Steel Stopper
On/Off Control	Wall Switch or Built-In Air Switch		
Motor	Single Phase	Grind Chamber Capacity	1180 ml
Reversing	Auto-Reverse Grind System	Motor Protection	Manual Reset Overload
Time Rating	Intermittent	Average Water Usage	Approximately 1% of household water consumption
Lubrication	Permanently Lubricated Upper & Lower Bearings	Average Electrical Usage	3-4 KWH p.a, equal to approx. \$3.50 p.a
Shipping Weight (Approx.)	11.4 kg	Drain Connection	1-1/2" (3.81 cm) Anti-Vibration (Hose Clamp)
Unit Finish	Stainless Steel Light Gray	Dishwasher Drain Connection	No
Overall Height	33.0 cm		
Grind Technology	3-Stage Grind Technology Jam Preventing Circuit		

Volts/Hz	HP	Average Load
120V, 60 Hz	1.0	10.2 A
220-240V, 50-60 Hz	.75 (@240V/50Hz)	370 W

InSinkErator Australia
Sales/Service Tel: 1300 136 205

www.insinkerator.com.au



InSinkErator reserves the right to change product specifications without prior notice. All products are for household use: usage in commercial situations is not covered by warranty.